


# CAB-586 Cable Kit

for the APx586 multichannel audio analyzer



## Contents

- A) 1 each DB25M to 8 XLR-M breakout cable
- B) 2 each DB25M to 8 XLR-F breakout cable
- C) 1 each Toslink optical cable
- D) 11 each BNC-M to BNC-M analog or digital coax loopback cables
- E) 2 each XLR-M to XLR-F balanced digital audio cables
- F) 1 each DB25M to DB25M balanced cable for loopback or AUX-0100 filter use. Required for AUX-0100.
- G) 1 each ground strap; 26 each BNC-M to RCA-F adapters



5750 SW Arctic Drive  
Beaverton OR 97005  
1-800-231-7350  
sales@ap.com  
www.ap.com